

S A F E A N D S O U N D

H O T E L S A F E

**Electronic Digital Lock (EDL) offers Comfort, Convenience and Reliability.
EDL can be programmed with Access Code only entered by the User.
Your guest deserves Maximum Security.**




H O T E L S A F E

hotel safe is also used a private safe at home

Hotel Safe is

- Easy to use, and maintenance free.
- Quick to enter a user's personal code.
- A Changeable Master Code provides Emergency Override Procedures to Hotel Management.
- Opening attempts with wrong codes over 5 times by an unauthorized person make the lock get frozen.
- But, the user need not worry about it. He only can reactivate the lock by pushing his right code twice in sequence.
- Anchored on the wall or on the floor with two anchoring bolts.



How to ENTER your Personal Code?

- 1st : Push Memory Button **M** on backside of door (LED flickers and it sound Bi).
- 2nd : Enter your personal code (4 digits Min, 16 digits Max).
- 3rd : Push Finish Button **#** (Melody Rings).

- *Caution : To confirm if the personal code is entered exactly, push buttons in opening procedures prior to closing door. For example, in case of your personal code 2000, push buttons C2000#. If procedures are properly done, melody rings four seconds.*

How to OPEN (or CLOSE) Door?

- 1st : Push Start Button **C** (LED flickers with Bi sound).
- 2nd : Push Your Personal Code (LED flickers with Bi sound).
- 3rd : Push Finish Button **#** (Melody rings).
- 4th : Turn knob clockwise (or counter-clockwise) and Pull (or push) Door while Melody Rings.

- *In case of wrong code tried over 5 times, lock gets frozen, and keeps quiet until released. To release lock from frozen state, proceed above opening steps twice consecutively.*

(Ex. In case of personal code **1234**, push buttons **C1234#C1234#**)

- *In case of Private Safe, user need not enter personal code to close door.*



SPECIFICATION

Model	high	wide	deep	Weight	Capacity	Remarks
	(mm/inch)			(Kgs/lbs)	(l/inch ³)	
H25	250	360	320 *	13	21.7	Non-Insulated
	9.8	14.2	12.6 *	29	1324	
H30	300	420	380 *	17	38	Non-Insulated
	11.8	16.5	15.0 *	37	2319	
P25	P-Model is for private use at home.					
P30	Its dimension is the same as that of H-Model, but its locking system is different.					

* Including Key-Board